



**VIET TECHNOLOGY RESEARCH AND DEVELOPMENT CENTER**  
**VIETSON MACHINERY MANUFACTURING CO., LTD**  
Web: [www.vietson.com.vn](http://www.vietson.com.vn) Email: [vietson@vietson.com.vn](mailto:vietson@vietson.com.vn)



## DISINFECTION BOX

ULTRASONIC ATOMIZER MIST TECHNOLOGY

V-UM1 MODEL



## CONTACT US

### VIETSON MACHINERY MANUFACTURING CO., LTD

Địa chỉ: N7 Str., Tân Phú Trung Industrial Zone,  
Cu Chi Dist., HoChiMinh city, Vietnam

Web: [www.vietson.com.vn](http://www.vietson.com.vn)

Mail: [vietson@vietson.com.vn](mailto:vietson@vietson.com.vn)

Phone/ Zalo/ Viber: **096 3934 232**

## TECHNICAL DATA

ITEMS	V-UM1
Dimension (WxHxD)	1.04mx2.34mx1.26m
Frame material	Galvanised steel
Wall material	Transparent Polyvinyl chloride (PVC)
Curtain material	Transparent Polyvinyl chloride (PVC)
Floor material	Inox
Antiseptic solution	Anolyte 200
Misting power	40ml/20 seconds
Entrance and exit door	2

## WORKING FLOW

Green light  
indicates

Identification  
sensor

Duration: 20 seconds

Red light  
indicates

Wait  
outside



Enter  
the box



Ultrasonic Mist  
Maker work



Turn around (one circle)  
during the time system works



Get  
outside

## FEATURES

- Disinfected by **ULTRASONIC ATOMIZER MIST TECHNOLOGY**, saving disinfectant solution, un-wet clothes
- **ANOLYTE SOLUTION** (Electro-Chemical Activation) has high antibacterial, antiseptic.
- **AUTOMATICALLY WORKS** when having people inside
- **INDICATOR LIGHTS AND ALARM** during operation
- Allows changing the **OPERATING TIME** from **20-30 seconds**
- Low antiseptic solution **WARNING SENSOR**
- Equipped with **AUTOMATIC LIQUID TOUCHLESS SOAP DISPENSER** before entering the box (Option)